


## **ICSN-3** ISOTECH COOLING TOWER/CHILLER NON-SEISMIC

File No.: ISCOS-ICSN-3-5000-9000

Date:03/29/22

ISOIN-ICSN-3-5000-9000, Installation Instructions Document, to be Reviewed for Installation

SPECIFICATIONS: ICSN-3" DEFLECTION RESTRAINED SPRING ISOLATOR											
Model	Rated Load		Rated Deflection		Spring Color		Approx. WT.				
	lbf.	kN	in	mm	outer	inner	Lbs.	kg			
ICSN-3-5000	5000	22.241	3.0	76.2	GREY		99.00	44.91			
ICSN-3-5600	5600	24.91	3.0	76.2	GREY	WHITE	100.60	45.64			
ICSN-3-6000	6000	26.69	3.0	76.2	BROWN		100.00	45.36			
ICSN-3-7000	7000	31.138	3.0	76.2	BROWN	YELLOW	101.40	46.00			
ICSN-3-7600	7600	33.807	3.0	76.2	BROWN	GERY	101.80	46.18			
ICSN-3-8000	8000	35586	3.0	76.2	BROWN	RED	102.24	46.38			
ICSN-3-9000	9000	40.034	3.0	76.2	BROWN	BLACK	105.00	47.63			



- ICSN-3-5000-9000 type isolators are designed for minimum 1g lateral seismic and wind load when attached to steel structure. Housing is made from high strength steel
- ICSN-3-5000-9000 Isolators are all Pre-Compressed to allow the lowest overall installation height and to offer significant labor saving during installation

  All springs have additional travel to solid equal to 50% of the Rated Deflection with minimum Kx/Ky ratio of 1.0 All Elements are safe at solid load
- $\bullet \ Spring(s) \ are powder-coated to provide maximum corrosion resistance\ , and are color-coded for easy identification at site-see table above$
- Hot-Dip Galvanized finish for Housing to offer maximum corrosion resistance for isolator Hardware and Spring Compression Cup are zinc -electroplated
- ICSN-3-5000-9000 isolators are designed to allow replacement of Neoprene grommet without disturbing equipment. Neoprene grommet are installed to prevent metal to metal contact
- Same Thickness and dimensions of isolator top plate, must be installed on top of isolator, when less than 80% of isolator's top plate is covered.

		·	•	•		
PROJECT INFORMATION		EQUIPMENT INFOR	MATION	CANADA	UNITED STATES	
Customer:		Type:		8 High Meadow Place,	800-7700 Irvine Center Dr.	••
Proiect:		Oty Required:		North York, ON M9L 2Z5,	Irvine, CA 92618,	
,,,,,				C: 416-831-3000	U.S.A. C: 714-264-8090	
Drawing No:		Operating Weight:				
Notes:		www.isotechindustries.com				

COPYRIGHT: UNLESS OTHERWISE AGREED OR STATED IN WRITING, ALL INFORMATION AND DESIGNS DISPLAYED WITHIN ARE ALL THE PROPERTY OF ISOTECH INDUSTRIES INC. AND MAY NOT BE DUPLICATED OR DISTRIBUTED OUTSIDE OF ISOTECH INDUSTRIES INC. WITH THE EXCEPTION OF AUTHORIZED PERSONS WITH LEGITIMATE NEED TO KNOW WHO BY THE USE OF THIS RECOGNIZE ISOTECH INDUSTRIES INC. OWNERSHIP AND WILL COMPLY TO MAINTAIN THIS INFORMATION AND DESIGN IN STRICT CONFIDENCE.